



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1/2X45 (1.3/4)

Numero articolo 22085.127.044

Marchio -

UBB 500578756636

UNSPSC 31161619

EAN 8715494376594

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	1/2 Inch
Lunghezza	45 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	13

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

Specifica tecnica

B 0.875

Disegno tecnico

L (mm)	45
M	12.3

