



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1 Inch X275 (10.3/4)

Numero articolo 22085.254.273

Marchio -

UBB 500578787250

UNSPSC 31161619

EAN 8715494389594

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	1 Inch
Lunghezza	275 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	8

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

Specifica tecnica

B 1.625

Disegno tecnico

L (mm) 275

M 25

