



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.7 1.1/8X295 (11.1/2)

Numero articolo 22326.285.292

Marchio -

UBB 500578271776

UNSPSC 31161619

EAN 8715494360647

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	1.1/8 Inch
Lunghezza	295 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info
Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

Specifica tecnica

B	1.8125
L (mm)	295

Disegno tecnico

