



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8 Cl.2 - Gr.8 1/2X70 (2.3/4)

Numero articolo 22529.127.069

Marchio -

UBB 500578414426

UNSPSC 31161619

EAN 8715494349475

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	1/2 Inch
Lunghezza	70 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	13

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	--

Standard

ASME B16.5/B18.2.2

ASTM A193/A194

BS ≈4882

Specifica tecnica

B 0.875

L (mm) 70

Disegno tecnico

