



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A320 - ASTM A194 Gr.B8 Cl.2 - Gr.8 5/8X40 (1.1/2)

Numero articolo 22531.158.038

Marchio -

UBB 500578597824

UNSPSC 31161619

EAN 8715494358682

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	5/8 Inch
Lunghezza	40 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	11

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	--

Standard

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Specifica tecnica

B	1.0625
L (mm)	40

Disegno tecnico

