



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8M Cl.2 - Gr.8M 1.1/8X590 (23.1/4)

|                 |               |
|-----------------|---------------|
| Numero articolo | 22539.285.590 |
| Marchio         | -             |
| UBB             | 500578141755  |
| UNSPSC          | 31161619      |
| EAN             | 8715494326483 |
| PKG. di 1       | Solo full box |

### Parametri tecnici:

|                    |                                                                                                                                                                                                                  |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Diametro           | 1.1/8 Inch                                                                                                                                                                                                       |
| Lunghezza          | 590 mm                                                                                                                                                                                                           |
| Class              | Gr.B8M Cl.2 - Gr.8M                                                                                                                                                                                              |
| Material           | Stainless steel                                                                                                                                                                                                  |
| Material technical | ASTM A193 - ASTM A194                                                                                                                                                                                            |
| Thread direction   | Right                                                                                                                                                                                                            |
| Thread             | 8 Unified National                                                                                                                                                                                               |
| Threads per inch   | 8                                                                                                                                                                                                                |
| Info               | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |

### Standard

|      |               |
|------|---------------|
| BS   | ≈4882         |
| ASTM | A193/A194     |
| ASME | B16.5/B18.2.2 |

### Specifica tecnica

|   |        |
|---|--------|
| B | 1.8125 |
|---|--------|

### Disegno tecnico

L (mm) 590

M 28.2

