



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8M Cl.2 - Gr.8M 1.3/8X260 (10.1/4)

Numero articolo 22539.349.260

Marchio -

UBB 500578153701

UNSPSC 31161619

EAN 8715494326858

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	1.3/8 Inch
Lunghezza	260 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Specifica tecnica

B 2.1875

Disegno tecnico

L (mm) 260

M 34.1

