



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B16 - Gr.4 3/8X70 (2.3/4)

Numero articolo 22554.096.069

Marchio -

UBB 500579037887

UNSPSC 31161619

EAN 8715494413350

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	3/8 Inch
Lunghezza	70 mm
Class	Gr.B16 - Gr.4
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	16

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased

Standard

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

FABORY

out gradually.
It is advised to
use Grade 7 nuts
instead.

Specifica tecnica

B	0.6875
L (mm)	70
M	9

Disegno tecnico

