



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B16 - Gr.4 1.1/8X415 (16.1/4)

Numero articolo	22555.285.412
Marchio	-
UBB	500578207762
UNSPSC	31161619
EAN	8715494350136
PKG. di 1	Solo full box

Parametri tecnici:

Diametro	1.1/8 Inch
Lunghezza	415 mm
Class	Gr.B16 - Gr.4
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Standard

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

FABORY It is advised to
use Grade 7 nuts
instead.

Specifica tecnica

B	1.8125
L (mm)	415
M	28.2

Disegno tecnico

