



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B16 - Gr.4 1.1/4X440 (17.1/4)

Numero articolo 22555.317.438

Marchio -

UBB 500578217746

UNSPSC 31161619

EAN 8715494356107

PKG. di 1 Solo full box

### Parametri tecnici:

Diametro	1.1/4 Inch
Lunghezza	440 mm
Class	Gr.B16 - Gr.4
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

### Standard

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

**FABORY** It is advised to  
use Grade 7 nuts  
instead.

### Specifica tecnica

B	2
L (mm)	440
M	31

### Disegno tecnico

