



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X50

Numero articolo 24540.060.050

Marchio -

UBB 950353137744

UNSPSC 31161504

EAN 8715492633712

PKG. di 200 Solo full box

Parametri tecnici:

Diametro	M6
Lunghezza	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standard

ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
ISO	≈2009
NEN	≈2370
DIN	963

Specifica tecnica

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	50
n	1.6
P	1
t (min.)	1.2

Disegno tecnico

