



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M2X8

Numero articolo 24662.020.008

Marchio -

UBB 500654327542

UNSPSC 31161504

EAN 8712423009899

PKG. di 1000 Solo full box

Parametri tecnici:

Diametro	M2
Lunghezza	8 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standard

ISO	≈7045
DIN	7985

Specifica tecnica

d-D	M2
Thread length (min.)	16
dk (max.)	4
Full thread if $L \leq$	18
k	1.6
L (mm)	8
No. cross recess	1
P	0.4

Disegno tecnico

