



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 M4X10

Numero articolo 24691.040.010

Marchio -

UBB 951353509320

UNSPSC 31161504

EAN 8715492643506

PKG. di 200 Solo full box

Parametri tecnici:

Diametro	M4
Lunghezza	10 mm
Class	4.8
Driving features	Phillips
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standard

NF	≈E25-120
DIN	966
ISO	≈7047

Specifica tecnica

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	10
No. cross recess	2
P	0.7

Disegno tecnico

