

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M5X25

Numero articolo	24810.050.025
Marchio	-
UBB	950353875541
UNSPSC	31161504
EAN	8715492645050
PKG. di 200	Solo full box

Parametri tecnici:

Diametro	M5
Lunghezza	25 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standard

ISO	≈7045
DIN	7985

Specifica tecnica

d-D	M5
Thread length (min.)	25
dk (max.)	10
Full thread if $L \leq$	28
k	3.8
L (mm)	25
No. cross recess	2
P	0.8

Disegno tecnico

