



HECO-FIX Cross recessed raised cheese head screw for chipboard Steel Zinc plated 3X15MM

Numero articolo 29345.030.015

Marchio -

UBB 950350323412

UNSPSC 31161508

EAN 4019787051545

PKG. di 200 Solo full box

Parametri tecnici:

Diametro	3 mm
Lunghezza	15 mm
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated

Standard

Info	All dimensions are guide values and may deviate dependent on the manufacturer. Specific features HECO-FIX PLUS screws for chipboard: Reduction of required drive torque of up to 30%. Easier handling. Substantially higher screwing performance on using storage battery screw drivers. Axial forces are reduced, thereby less wear of screw driver bits. By means of the tooth geometry, a higher unscrewing moment is nevertheless,
------	--

achieved and consequently, a secure screwed connection is obtained. Warning: electro-galvanizing of these products may cause hydrogen embrittlement.

Specifica tecnica

D (mm)	3
dk (max.)	5.9
k (max.)	2.2
L (mm)	15
No. cross recess	1

Disegno tecnico

