



MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Steel Zinc plated ST3,9X25MM

Numero articolo 30300.039.025

Marchio -

UBB 500618323959

UNSPSC 31161507

EAN 8715494501811

PKG. di 200 Solo full box

Parametri tecnici:

Diametro	3.9 mm
Lunghezza	25 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Full boxes only.

Standard

ISO	≈15482 H
DIN	≈7504-O H

Specifica tecnica

D (mm)	3.9
dk	8
k	2.6
L (mm)	25
L1	4.5
No. cross recess	2

Disegno tecnico

