

MAXXFAST Anchor bolt
ThruMaxx Steel Zinc plated
ETA-7 6X70



Article number	30551.060.070
Brand	-
UBB	500577352551
UNSPSC	31162101
EAN	8715494322959
PKG. of 200	Full Box Only

Technical Parameters

Diameter	6 mm
Length	70 mm
Material	Steel
Approval	ETA Option 7
Surface treatment	Zinc plated
Thread	Metric thread

Standards

Info	Full boxes only. do = Nominal diameter of drill bits = Width across flats ring ø = Washer diameter df = Diameter of clearance hole in the fixture h1 = Recommended drilling depth h(nom) = Minimum hole depth h _{ef} = Effective anchorage depth s _{c,r,N} = Spacing characteristic c _{c,r,N} = Edge distance characteristic t _{fix(max)} = Grip range T _{inst} = Tightening torque in Nm N _{rec} = Recommended load in kN The allowable load is valid for
------	--

one single anchor,
at non-cracked
concrete (pressure
zone) with concrete
class C20/25, incl.
partial safety factor
 $\gamma_f = 1,4$ and if the
Scr, N and Ccr,
N are taken in to
account.ETA-7

Technical Specification

Ccr, N	60
d-D	M6
df	7
D (mm)	6
do	6
h (nom.)	49.5
h1	55
hef	40
L (mm)	70
Nrec	3.93
Ring ø	12
s	10
Scr, N	120
tfix(max.)	12
Tinst	7

Technical Drawing

