

MAXXFAST Anchor bolt ThruMaxx Stainless steel A4 ETA-7 12X140



Numero articolo	30553.120.140
Marchio	-
UBB	500577357840
UNSPSC	31162101
EAN	8715494323482
PKG. di 25	Solo full box

Parametri tecnici:

Diametro	12 mm
Lunghezza	140 mm
Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread

Standard

Info

Full boxes only.
do = Nominal diameter
of drill bits = Width
across flats
ring $\varnothing$ = Washer diameter
df = Diameter of
clearance hole
in the fixture
h1 = Recommended
drilling depth
h(nom) = Minimum
hole depth
hef = Effective anchorage
depth
Scr,N = Spacing
characteristic
Ccr,N = Edge distance
characteristic
tfix(max) = Grip range
Tinst = Tightening torque
in Nm
Nrec = Recommended load
in kN
The allowable
load is valid for
one single anchor,
at non-cracked

FABORY

concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account. ETA-7

Specifica tecnica

Ccr, N	98
d-D	M12
df	14
D (mm)	12
do	12
h (nom.)	77
h1	85
hef	65
L (mm)	140
Nrec	9.92
Ring ø	24
s	19
Scr, N	195
tfix(max.)	48
Tinst	60

Disegno tecnico

