



Clamp-adjusting ring with two hexagon socket head cap screws Free-cutting steel 20

Numero articolo	37845.200.001
-----------------	---------------

Marchio	-
---------	---

UBB	500501979743
-----	--------------

UNSPSC	31161807
--------	----------

EAN	8715494229432
-----	---------------

PKG. di 5	Solo full box
-----------	---------------

Parametri tecnici:

Diametro	20 mm
Material	Free-cutting steel
Outer diameter	45

Info	Special features of clamp-adjusting rings: Easy assembly and disassembly, precise positioning, very strong connection without clearance. Equal distribution of the clamping force over the circumference of the shaft, compensate for tolerance variations. They cause no damage to the shaft during assembly as shaft metal is not deformed. The clamp-adjusting rings are supplied with one hexagon socket head cap screw to ISO 4762 (DIN 912), class 12.9.
------	--

Standard

Specifica tecnica

b	12
b (j14)	12
d1	20
d2	45
d2 (h13)	45
D (mm)	20
Screw size	M5x20
Thickness	12

Disegno tecnico

