



Split pin (cotter pin) DIN 94 Brass 2X25MM

Numero articolo	50210.020.025
Marchio	-
UBB	950359159098
UNSPSC	31163204
EAN	8715492241788
PKG. di 500	Solo full box

Parametri tecnici:

Diametro	2 mm
Lunghezza	25 mm
Material	Brass

Info

The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of the nominal length (L) is js17.

Standard

ISO	1234
NEN	182
NF	E25-774
DIN	94

Specifica tecnica

a (max.)	2.5
b $\approx$	4

Disegno tecnico

c (max.)	3.6
c (min.)	3.2
d (min.)	1.7
D (mm)	2
L (mm)	25
d (max.)	1.8

