



## Hexagon socket head cap screw with low head and pilot recess DIN 6912 Stainless steel A2 M8X70

Numero articolo	51042.080.070
-----------------	---------------

Marchio	-
---------	---

UBB	951351903533
-----	--------------

UNSPSC	31161605
--------	----------

EAN	8715492261212
-----	---------------

PKG. di 10	Solo full box
------------	---------------

### Parametri tecnici:

Diametro	M8
Lunghezza	70 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

### Standard

DIN	6912
-----	------

**Info**

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

## Specifica tecnica

b (min.):  $L \leq 125\text{mm}$  22

d-D M8

dh 4

dk 13

Full thread if  $L \leq$  30

k 5

L (mm) 70

P 1.25

s 6

## Disegno tecnico

