



Hexagon socket countersunk head screw ISO 10642 Stainless steel A2 M8X70

Numero articolo	51060.080.070
Marchio	-
UBB	951351980184
UNSPSC	31161518
EAN	8715492265210
PKG. di 50	Solo full box

Parametri tecnici:

Diametro	M8
Lunghezza	70 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standard

ISO	10642
-----	-------

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

b (min.)	28
d-D	M8
dk (max.)	16.43
Full thread if $L \leq$	45
k (max.)	4.96
L (mm)	70
P	1.25
s	5
α	90

Disegno tecnico

