



Hexagon socket countersunk head screw ISO 10642 Stainless steel A2 M16X45

Numero articolo	51060.160.045
Marchio	-
UBB	950351802315
UNSPSC	31161518
EAN	8715492265616
PKG. di 25	Solo full box

Parametri tecnici:

Diametro	M16
Lunghezza	45 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standard

ISO	10642
-----	-------

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

b (min.)	48
d-D	M16
dk (max.)	30.61
Full thread if $L \leq$	70
k (max.)	8.8
L (mm)	45
P	2
s	10
α	90

Disegno tecnico

