



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1,2X5

Numero articolo 51120.012.005

Marchio -

UBB 950353255397

UNSPSC 31161504

EAN 8715492270627

PKG. di 100 Solo full box

Parametri tecnici:

Diametro	M1.2
Lunghezza	5 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standard

ASME	≈B18.6.7M
NF	≈E25-127
NEN	≈1602
ISO	≈1207
DIN	84
BS	≈4183

Specifica tecnica

d-D	M1.2
Thread length (min.)	25
dk (max.)	2.3
Full thread if L ≤	30
k (max.)	0.8
L (mm)	5
n	0.3
P	0.25
t (min.)	0.3

Disegno tecnico