



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1,6X10

Numero articolo	51120.016.010
Marchio	-
UBB	950353256205
UNSPSC	31161504
EAN	8715492270733
PKG. di 100	Solo full box

Parametri tecnici:

Diametro	M1.6
Lunghezza	10 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standard

DIN	84
ASME	≈B18.6.7M
NEN	≈1602
ISO	≈1207
BS	≈4183
NF	≈E25-127

Specifica tecnica

d-D	M1.6
Thread length (min.)	25
dk (max.)	3
Full thread if L ≤	30
k (max.)	1
L (mm)	10
n	0.4
P	0.35
t (min.)	0.45

Disegno tecnico