

Hexagon nut left hand thread DIN 934 Stainless steel A2 70 M5 (LH)

Numero articolo	51162.050.001
Marchio	-
UBB	950355596574
UNSPSC	31161727
EAN	8715492274120
PKG. di 100	Solo full box

Parametri tecnici:

Diametro	M5
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Left
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.left hand thread

Standard

NF	E25-401
NEN	1560
DIN	934

Specifica tecnica

d-D	M5
m	4
P	0.8
s	8

Disegno tecnico

