



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M1,6X12

Numero articolo 51302.016.012

Marchio -

UBB 951353116944

UNSPSC 31161504

EAN 8715492281890

PKG. di 1000 Solo full box

Parametri tecnici:

Diametro	M1.6
Lunghezza	12 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standard

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Specifica tecnica

d-D	M1.6
Thread length (min.)	15
dk (max.)	3
Full thread if L ≤	16
k (max.)	0.96
L (mm)	12
No. cross recess	0
P	0.35

Disegno tecnico

