



Spring-type straight pin slotted, heavy duty, stainless spring steel DIN ≈1481 Stainless spring steel 10X18MM

Numero articolo	51428.100.018
Marchio	-
UBB	500635845729
UNSPSC	31163201
EAN	8717077786370
PKG. di 500	Solo full box

Parametri tecnici:

Standard

Diametro	10 mm	DIN	≈1481
Lunghezza	18 mm	ISO	≈8752
Material	Stainless spring steel	BS	≈7060
Info	Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 8$ mm a single chamfer configuration is optional at the discretion of the manufacturer. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these	NEN	≈2458

pins are employed
with bolted joints the
below arrangement
should be used:

Specifica tecnica

a	2
d1 (max.)	10.8
d1 (min.)	10.5
d2 ≈	6.5
D (mm)	10
L (mm)	18
s	2

Disegno tecnico

