



Grooved pin, full length parallel with chamfer DIN 1473 Stainless steel A1 1,5X8MM

Numero articolo	51582.015.008
Marchio	-
UBB	500696078079
UNSPSC	31163215
EAN	8715492046185
PKG. di 500	Solo full box

Parametri tecnici:

Lunghezza	8 mm
Material	Stainless steel
Material technical	A1

Standard

NEN	≈2604
DIN	1473
ISO	≈8740

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Specifica tecnica

c ≈	0.2
d1	1.5
d2 ≈	1.6
f ≈	0.8

Disegno tecnico

L (mm)	8
r	1.5
Tolerance	h9
V	1.6

