



Grooved pin, one-third length center grooved DIN 1475 Stainless steel A1 5X18MM

Numero articolo 51587.050.018

Marchio -

UBB 500697303518

UNSPSC 31163215

EAN 8715492081223

PKG. di 200 Solo full box

Parametri tecnici:

Lunghezza	18 mm
Material	Stainless steel
Material technical	A1

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standard

ISO	≈8742
DIN	1475
NEN	≈2606

Specifica tecnica

c ≈	0.6
d1	5
d2 ≈	5.3
L (mm)	18

Disegno tecnico

$r \approx$	5
Tolerance	$h11$
V	16.5

