

Hexagon head bolt DIN 931 Stainless steel A4 80 M10X90

Numero articolo	53510.100.090
Marchio	-
UBB	950351832197
UNSPSC	31161620
EAN	8715492318046
PKG. di 50	Solo full box

Parametri tecnici:

Diametro	M10
Lunghezza	90 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standard

ISO	4014
NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M

Specifica tecnica

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	90
P	1.5
s	17

Disegno tecnico

