



Hexagon socket head cap screw with low head and pilot recess DIN 6912 Stainless steel A4 M6X30

Numero articolo 55042.060.030

Marchio -

UBB 952351086105

UNSPSC 31161605

EAN 8715492327048

PKG. di 50 Solo full box

Parametri tecnici:

Diametro	M6
Lunghezza	30 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standard

DIN 6912

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Specifica tecnica

b (min.): $L \leq 125\text{mm}$ 18

d-D M6

dh 3

dk 10

Full thread if $L \leq$ 25

k 4

L (mm) 30

P 1

s 5

Disegno tecnico

