



Hexagon socket head cap screw with low head and pilot recess DIN 6912 Stainless steel A4 M16X35

Numero articolo	55042.160.035
Marchio	-
UBB	952351088838
UNSPSC	31161605
EAN	8715492327314
PKG. di 5	Solo full box

Parametri tecnici:

Diametro	M16
Lunghezza	35 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standard

DIN	6912
-----	------

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Specifica tecnica

b (min.): 44
125mm $L \leq 200$ mm

b (min.): L200mm 57

b (min.): $L \leq 125$ mm 38

d-D M16

dh 8

dk 24

Full thread if $L \leq 50$

k 10

L (mm) 35

P 2

s 14

Disegno tecnico

