



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M1,6X12

Numero articolo	55050.016.012
Marchio	-
UBB	500571288991
UNSPSC	31161605
EAN	8715494141154
PKG. di 500	Solo full box

Parametri tecnici:

Diametro	M1.6
Lunghezza	12 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standard

BS	4168-1
NEN	1241
NF	E25-125
ASME	B18.3.1M
DIN	912
ISO	4762

Specifica tecnica

b	15
d-D	M1.6
dk (max.)	3
Full thread if $L \leq$	16
k (max.)	1.6
L (mm)	12
P	0.35
s	1.5

Disegno tecnico

