



Hexagon socket countersunk head screw ISO 10642 Stainless steel A4 M2,5X4

Numero articolo	55060.025.004
-----------------	---------------

Marchio	-
---------	---

UBB	500696105385
-----	--------------

UNSPSC	31161518
--------	----------

EAN	8715492053381
-----	---------------

PKG. di 1000	Solo full box
--------------	---------------

Parametri tecnici:

Diametro	M2.5
Lunghezza	4 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standard

ISO	10642
DIN	≈7991

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

d-D	M2.5
dk (max.)	5.08
Full thread if $L \leq$	25
k (max.)	1.69
L (mm)	4
P	0.45
s	1.5
α	90

Disegno tecnico

