



Hexagon socket countersunk head screw ISO 10642 Stainless steel A4 M3X10

Numero articolo	55060.030.010
-----------------	---------------

Marchio	-
---------	---

UBB	952351392438
-----	--------------

UNSPSC	31161518
--------	----------

EAN	8715492330017
-----	---------------

PKG. di 200	Solo full box
-------------	---------------

Parametri tecnici:

Diametro	M3
Lunghezza	10 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standard

DIN	≈7991
ISO	10642

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if $L \leq$	25
k (max.)	1.86
L (mm)	10
P	0.5
s	2
α	90

Disegno tecnico

