



## Slotted countersunk head screw DIN 963 A Stainless steel A4 M5X40

|                 |               |
|-----------------|---------------|
| Numero articolo | 55110.050.040 |
| Marchio         | -             |
| UBB             | 950353293257  |
| UNSPSC          | 31161504      |
| EAN             | 8715492333933 |
| PKG. di 200     | Solo full box |

### Parametri tecnici:

|                    |                  |
|--------------------|------------------|
| Diametro           | M5               |
| Lunghezza          | 40 mm            |
| Class              | 70               |
| Driving features   | Slotted          |
| Head shape         | Countersunk head |
| Material           | Stainless steel  |
| Material technical | A4               |
| Thread             | Metric thread    |

### Standard

|      |           |
|------|-----------|
| DIN  | 963       |
| NF   | ≈E25-123  |
| NEN  | ≈2370     |
| ASME | ≈B18.6.7M |
| ISO  | ≈2009     |
| BS   | ≈4183     |

### Specifica tecnica

|                         |     |
|-------------------------|-----|
| d-D                     | M5  |
| Thread length (min.)    | 25  |
| dk (max.)               | 9.2 |
| Full thread if $L \leq$ | 30  |
| k (max.)                | 2.5 |
| L (mm)                  | 40  |
| n                       | 1.2 |
| P                       | 0.8 |
| t (min.)                | 1   |

### Disegno tecnico

