



Slotted pan head screw DIN 85 Stainless steel A4 70 M3X20

Numero articolo	55140.030.020
Marchio	-
UBB	950353307602
UNSPSC	31161504
EAN	8715492335920
PKG. di 500	Solo full box

Parametri tecnici:

Diametro	M3
Lunghezza	20 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standard

ASME	≈B18.6.7M
NF	≈E25-128
ISO	≈1580
NEN	≈1603
DIN	85
BS	≈4183

Specifica tecnica

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	20
n	0.8
P	0.5
t (min.)	0.7

Disegno tecnico

