



KIPP Clamping levers 20 degrees, external thread Silver metallic Die cast zinc/ steel 5.8 Plastic coated/black oxide M6X13X10

Numero articolo 58029.060.010

Marchio -

UBB 500689482858

UNSPSC 31162807

EAN 4059245078189

PKG. di 10 Solo full box

Parametri tecnici:

Class	5.8
Color title	Silver metallic
D1_MM	13mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8. Version: Handle plastic coated. Steel parts black oxidized.

Standard

Specifica tecnica

A	39
A1	46
D	10
D1	13
D2	14
D3	10.5
H	24.5
H2	15

Disegno tecnico

H3	32.5
H4	35.5
H1	4
Number of teeth	16
L	10
X	6

FABORY

