



FISCHER Anchor bolt Steel Zinc plated FAZII16/100

Numero articolo 63323.160.100

Marchio -

UBB 500504262667

UNSPSC 31162101

EAN 4006209958650

PKG. di 10 Solo full box

Parametri tecnici:

Standard

Material	Steel
Approval	ETA Option 1
Surface treatment	Zinc plated
Thread	Metric thread
Tipo no.	FAZ II

Info do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval

is also available on
request.

FABORY

Specifica tecnica

d-D	M16
do	16
hef	85
kN	13.4
L (mm)	225
Min. td	215
Ring ø	30
s	24
tfix	100
Type	FAZII16/100

Disegno tecnico

