



FISCHER Anchor bolt Steel Zinc plated FAZII20/60

Numero articolo 63323.200.060

Marchio -

UBB 500504263244

UNSPSC 31162101

EAN 4006209466339

PKG. di 5 Solo full box

Parametri tecnici:

Standard

Material	Steel
Approval	ETA Option 1
Surface treatment	Zinc plated
Thread	Metric thread
Tipo no.	FAZ II

Info do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval

is also available on
request.

FABORY

Specifica tecnica

d-D	M20
do	20
hef	100
kN	17.1
L (mm)	200
Min. td	185
Ring ø	37
s	30
tfix	60
Type	FAZII20/60

Disegno tecnico

