



Blind rivet nut open, cylindrical head, round serrated body Steel Zinc plated 3 OCH 25

Numero articolo	69135.030.025
Marchio	-
UBB	500570649870
UNSPSC	31161703
EAN	8715494167192
PKG. di 250	Solo full box

Parametri tecnici:

Diametro	M3
Lunghezza	10.5 mm
Material	Steel
Surface treatment	Zinc plated

Standard

Specifica tecnica

Drill $\varnothing$	5
Grip range	0.5-2.5
$l [+0,5/-0]$	10.5
$\varnothing d$	3
$\varnothing dk$	7
Type	3 OCH 25

Disegno tecnico

