

Nagy teherbírású horgonycsavar, FH-B típus M16X95/165



Cikkszám	97296FIS
Márka	-
UBB	500616709027
UNSPSC	31162101
EAN	4006209972960
csom. 1	Csak bontatlan csomagban

Műszaki adatok

Átmérő	M16
Info	do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr}, N and C_{cr}, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available

Szabványok

FABORY

on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Műszaki **specifikációk**

Műszaki **rajz**

