



Studbolt with 2 heavy hexagon nuts ASTM A193/A194 Steel Zinc plated yellow passivated Gr.B7 - Gr.2H 3.1/2X760 (30)

Numero articolo PIMI2889760

Marchio -

UBB

UNSPSC

EAN

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	3.1/2 Inch
Lunghezza	760 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated yellow passivated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

ASTM A193/A194

Specifica tecnica

L (mm) 760

Disegno tecnico

FABORY

