



Studbolt with 2 heavy hexagon nuts ASTM A320/A194 Steel Zinc plated yellow passivated Gr.L7 - Gr.7 5/8X100 (4)

Numero articolo PIMM2158100

Marchio -

UBB

UNSPSC

EAN

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	5/8 Inch
Lunghezza	100 mm
Class	Gr.L7 - Gr.7
Material	Steel
Surface treatment	Zinc plated yellow passivated

Info Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

ASTM A320/A194

Specifica tecnica

L (mm) 100

Disegno tecnico

FABORY

