



Studbolt with 2 heavy hexagon nuts ASTM A193/A194 Stainless steel Plain Gr.B8T Cl.2 - Gr.8T 5/8X100 (4)

Numero articolo	PIMPM158100
Marchio	-
UBB	500649561676
UNSPSC	00000000
EAN	
PKG. di 1	Solo full box

Parametri tecnici:

Diametro	5/8 Inch
Lunghezza	100 mm
Class	Gr.B8T Cl.2 - Gr.8T
Material	Stainless steel
Surface treatment	Plain

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standard

ASTM A193/A194

Specifica tecnica

L (mm)	100
--------	-----

Disegno tecnico

FABORY

