



Spring-type straight pin (spiral pin) coiled, light duty ASME B18.8.2 Spring steel SAE 1070 3/32X3/8

Numero articolo	U39130.009.0037
Marchio	-
UBB	500626313901
UNSPSC	31162400
EAN	8712423099890
PKG. di 100	Solo full box

Parametri tecnici:

Lunghezza	3/8 Inch
A (nom.)	0.09375
Material	Spring steel
Material technical	SAE 1070
Info	Warning: electroplating of these products may cause hydrogen embrittlement. V = minimum double shear load in lb.

Standard

ASME	B18.8.2
------	---------

Specifica tecnica

A (max.)	0.106
B (max.)	0.091
C (ref.)	0.038
A (min.)	0.099
V	475

Disegno tecnico

