



Binnenzeskant passchroef UNC ASME B18.3 Staal Blank 012.9 (1/4)5/16X2.1/2

Artikelnummer 07116.063.063

Merk -

UBB 953351304563

UNSPSC 31161605

EAN 8715492066602

PKG. van 10 Alleen volledige verpakkingen

Technische parameters

Lengte	2.1/2 Inch
Klasse	012.9
Aandraaivoorziening	Binnenzeskant
Kopsoort	Cilinderkop
Materiaalsoort	Staal
Draadrichting	Rechts
Oppervlaktebedekking	Blank
Draadsoort	Unified National Coarse

Standaarden

ASME	B18.3
BS	2470

Info	Waarschuwing: bij het elektrolytisch behandelen van deze producten bestaat er gevaar voor het optreden van waterstofbrosheid. All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread
------	--

tolerance class for these screws is 3A, plating can cause thread fit problems.

Technische specificatie

A (max.)	0.438
D	0.3125
D1	0.25
E	0.438
H (max.)	0.219
J	0.15625
Gangen per Inch	20
D (min.)	0.3085
D (max.)	0.3105

Technische tekening

