



## Studbolt met 2 zeskantmoeren ASME B16.5/ B18.2.2 Roestvaststaal (RVS) ASTM A193 - ASTM A194 Rechts Gr.B8 Cl.2 - Gr.8 1.3/8X410 (16.1/8)

Artikel nummer	22530.349.410
Merk	-
UBB	500578549817
UNSPSC	31161619
EAN	8715494357616
PKG. van 1	Alleen volledige verpakkingen

### Technische parameters

Diameter (Inch)	1.3/8
Length (L)	410
Length (inch)	16.1/8

Remarks Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Klasse Gr.B8 Cl.2 - Gr.8

Materiaalsoort Roestvaststaal (RVS)

Materiaalsoort Technisch ASTM A193 - ASTM A194

Draadrichting Rechts

Draadsoort 8 Unified National

### Standaarden

BS	4882
ASTM	A193/A194
ASME	B16.5 / B18.2.2

**Technische specificatie**

**Technische tekening**

B	2.3/16
M	34.1
Gangen per Inch	8

