



Studbolt met 2 zeskantmoeren ASME B16.5/ B18.2.2 Roestvaststaal (RVS) ASTM A193 - ASTM A194 Rechts Gr.B8 Cl.2 - Gr.8 2 Inch X315 (12.1/2)

Artikel nummer	22530.508.317
Merk	-
UBB	500578577032
UNSPSC	31161619
EAN	8715494372749
PKG. van 1	Alleen volledige verpakkingen

Technische parameters

Diameter (Inch)	2 Inch
Lengthe (L)	315
Lengthe (inch)	12.1/2

Remarks Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Klasse Gr.B8 Cl.2 - Gr.8

Materiaalsoort Roestvaststaal (RVS)

Materiaalsoort Technisch ASTM A193 - ASTM A194

Draadrichting Rechts

Draadsoort 8 Unified National

Standaarden

ASME	B16.5 / B18.2.2
ASTM	A193/A194
BS	4882

Technische specificatie

Technische tekening

M	50
B	3.1/8
Gangen per Inch	8

